

TECHNICAL BULLETIN

EPOXICASTTM M3119-RWREWORKABLE UNDERFILL ENCAPSULANT

EPOXICASTTM M3119-RW is a reworkable epoxy underfill is designed for CSP and BGA applications. It cures quickly at moderate temperatures to minimize stress to other components. When cured, this material provides excellent mechanical properties to protect solder joints during thermal cycling. M3119RW has high Tg with moderate cure temperatures.

- One Component
- Fast cure at moderate temperatures
- Compatible with most Pb-free solders

High Tg

Room Temperature Flow Capability Long Work Life at Room Temperature

TYPICAL HANDLING PROPERTIES:

Epoxicast	M3119-RW
Viscosity at 25°C, cp	1000-1500
Pot life (500 gram) at 25°C, days	>1 week
Gel time (25 gram) at 100°C, min	10-15
Shelf Life @ -40°C months	12.

Recommended Cure 10 min @ 130°C Alternate Cure 3-5 min @ 175°C

TYPICAL CURED PROPERTIES:

(Tested @ 25°C unless otherwise indicated)

Color	Amber
Specific Gravity	1.15
Hardness, Shore D	83
Linear Shrinkage (%)	0.1
Lap Shear Strength, psi	1500
Water Absorption (24 hr at RT), %	0.02
Glass Transition Temperature, (°C)	106
Service temperature range, °C	-55 to 250
Coefficient of Thermal Expansion, 10 ⁻⁶ /°C	
Below Tg	55
Above Tg	>150
Dielectric Constant (1 kHz)	3.6
Dissipation Factor (1 kHz)	0.003
Volume Resistivity, ohm-cm	1.0×10^{16}

INSTRUCTIONS FOR USE:

- Frozen packages must be completely thawed before use.
- 2. Do not remove the cover of the syringe and let it thaw at room temperature for 5 to 20 minutes depend on quantity and size.
- Wipe any condensed moisture from the container and open the cover.
- 4. Proceed with the potting or encapsulating application and cure as recommended.
- Some difference in properties may occur with the alternate or other cure schedule.

AVAILABILITY:

Premixed and frozen - Packaged in 10cc and 30cc disposable syringes and ship in dry ice at -80°C.

STORAGE:

Optimal Storage: -20°C to -40°C. Storage below -80°C or greater than -15 °C can adversely affect product properties.

WARNING!

Adequate ventilation of workplace and ovens is essential. These materials may cause injury to the skin following prolonged or repeated contact and dermatitis in susceptible individuals. In case of skin contact, wash thoroughly with soap and water. For eyes, flush immediately with plenty of water for at least 10 minutes and seek medical attention. Refer to Material Safety Data Sheet (MSDS) for additional health and safety information.